

Product & Technical Configuration



Overview

Separate tubesheets connect the tube side and shell side, helping detect leakage and reduce cross-contamination risk. Suitable for clean heat transfer duties in pharmaceutical, beverage, electronic and semiconductor processes.

Technical Configuration

Item	Configuration
Brand	IKUSE
Tubesheet arrangement	Double tubesheets
Service	Heat transfer for clean process fluids
Applications	Pharmaceutical, chemical, electronic, beverage and semiconductor industries
Selection data	Fluids, cleanliness requirements, thermal duty, temperature, pressure and installation space

Double-tubesheet Construction



The tube side and shell side use separate tubesheet connections to reduce cross-contamination risk and facilitate leak detection.

Selection for Clean Processes

Determine the configuration from the fluids, cleanliness requirements, temperature, pressure, thermal duty and installation space.